

Saker Tab-Tension CineGrey 5D® Series Dimensions Table

Model Numbers	Screen Diag.	Aspect Ratio	Case Length (A)	View Width (A1)	Ceiling bracket hole distance (A2)	Screen Width (A3)	L/R black masking (A4)	Weight Bar Length (A5)	Overall H with ceiling Bracket (B)	View Height (B1)	Screen Height (B2)	Top black masking (B3)	Bottom black masking (B4)	End cap H with bracket (B5)	End cap W with ceiling bracket (C)	End cap H with ceiling bracket (C1)	Screen Material to Wall Distance (C2)	Weight bar diameter (C3)	Net Weight	Gross Weight	Length	Height	Width
Unit: inch																			lbs	lbs	Packaging Dimensions		
SKT120XH2D5-E12	120"	16:9	124.2	104.6	92.7	116.4	5.9	121.9	78.1	58.8	73.2	12.0	2.4	4.6	4.6	4.9	1.4	0.9	51.5	71.1	132.9	7.9	8.5
SKT135XH2D5-E10	135"	16:9	137.3	117.7	105.8	129.5	5.9	134.9	83.5	66.2	78.5	10.0	2.4	4.6	4.6	4.9	1.4	0.9	58.9	75.9	142.7	8.1	8.5
SKT150XH2D5-E6	150"	16:9	150.4	130.7	118.9	142.6	5.9	148.0	86.8	73.5	81.9	6.0	2.4	4.6	4.6	4.9	1.4	0.9	64.3	88.3	155.0	7.9	8.5
SKT150UH2D5-E6	150"	16:9	150.4	130.7	118.9	142.6	5.9	148.0	86.8	73.5	81.9	6.0	2.4	4.6	4.6	4.9	1.4	0.9	69.5	95.9	160.2	9.3	9.8
Unit: mm																			kgs	kgs			
SKT120XHD5-E12	120"	16:9	3155	2657	2355	2957	150	3095	1984	1494	1859	305	60	118	118	125	35	23	23.3	32.3	3376	200	215
SKT135XHD5-E10	135"	16:9	3487	2989	2687	3289	150	3427	2120	1681	1995	254	60	118	118	125	35	23	26.7	34.4	3625	205	215
SKT150XHD5-E6	150"	16:9	3819	3321	3019	3621	150	3759	2205	1868	2080	152	60	118	118	125	35	23	29.2	40.0	3938	200	215
SKT150UHD5-E6	150"	16:9	3819	3321	3019	3621	150	3759	2205	1868	2080	152	60	118	118	125	35	23	31.5	43.5	4070	235	250

The listed measurements are for general reference only. Please contact EliteProAV™ to verify product design and dimensions before attempting to integrate its products with any structural or furniture modification. Although a manufacturer may offer product advice, it may be taken or disregarded at the integrator's discretion. EliteProAV™ will not be held responsible or be otherwise liable for faulty installations. Screen materials may expand and contract slightly over time. Elite ProAV allows a 1.5% tolerance within the viewing surface.

