

Saker Tab-Tension AT4D Dimensions Table

Model Number	Nominal Diagonal	Aspect Ratio	Screen Material	Gain	Case Length (A)	View Width (A1)	Bracket hole distance (A2)	Screen Width (A3)	Screen Material Excess (A4)	Weight Bar Length (A5)	Distance between left end cap to fabric (A6)	Distance between right end cap to fabric (A7)	Overall Height w/ Bracket (B)	View Height (B1)	Screen Height (B2)	Top Black Masking Border (B3)	Bottom black masking border including weight bar (B4)	End cap Width w/ Bracket (C)	End cap Height w/ Bracket (C1)	Screen Material to Wall Distance (C2)	Weight Bar Diameter (C3)
Unit: inch																					
SKT110XHAD	110"	16:9	CineGrey 4D AT	1.1	110.3	95.9	78.8	99.8	1.4	104.9	4.7	4.7	75.2	53.9	67.9	12.0	3.5	4.6	5.7	1.4	0.9
SKT125XHAD	125"	16:9	CineGrey 4D AT	1.1	123.4	109.0	91.9	112.9	1.4	118.0	4.7	4.7	78.5	61.3	71.3	8.0	3.5	4.6	5.7	1.4	0.9
SKT135XHAD	135"	16:9	CineGrey 4D AT	1.1	132.1	117.7	100.6	121.6	1.4	126.7	4.7	4.7	80.4	66.2	73.2	5.0	3.5	4.6	5.7	1.4	0.9
SKT150XHAD	150"	16:9	CineGrey 4D AT	1.1	145.2	130.7	113.7	134.7	1.4	139.8	4.7	4.7	82.8	73.6	75.5	0.0	3.5	4.6	5.7	1.4	0.9
Unit: mm																					
SKT110XHAD	110"	16:9	CineGrey 4D AT	1.1	2801	2435	2001	2535	35	2665	120	120	1910	1370	1725	305	90	116	145	35	24
SKT125XHAD	125"	16:9	CineGrey 4D AT	1.1	3133	2767	2333	2867	35	2997	120	120	1995	1557	1810	203	90	116	145	35	24
SKT135XHAD	135"	16:9	CineGrey 4D AT	1.1	3355	2989	2555	3089	35	3219	120	120	2043	1681	1858	127	90	116	145	35	24
SKT150XHAD	150"	16:9	CineGrey 4D AT	1.1	3687	3321	2887	3421	35	3551	120	120	2103	1868	1918	0	90	116	145	35	24

Note: Data Error may be ±1"

The listed measurements are for general reference only. Please contact Elite ProAV to verify product design and dimensions before attempting to integrate its products with any structural or furniture modification. Although a manufacturer may offer product advice, it may be taken or disregarded at the integrator's discretion. Elite ProAV will not be held responsible or be otherwise liable for faulty installations. *Screen materials may expand and contract slightly over time. Elite ProAV allows a 1.5% tolerance within the viewing surface.*

